

Contact Keystone to Order

Guaranteed Compatibility

Filters from the original diffuser manufacturer ensure performance and fit.

Custom Sizes

Custom filter sizes built to meet your project needs in as little as 5 days.

Quick Delivery

Industry leading lead times with common sizes available in as little as 2 days.

**SCANTO
LEARN
MORE**



REPLACEMENT FILTER SELECTION


HEPA filters typically have a product label on the filter frame, which includes the serial number, part number, and performance specifications. This label is the most reliable way to obtain the information needed to order a replacement filter.

In the absence of the product label, follow the steps below to gather the filter construction details and refer to the list of available filters on the back of this form to order a suitable replacement through Keystone.

FILTER SELECTION STEPS:


STEP 1. Measure overall filter dimensions:

- Width (A): Parallel to the filter media pleats
- Length (B): Perpendicular to the filter media pleats




STEP 2. Determine filter seal type:

- RSR-Gel Seal: Roomside replaceable with a gel seal
- BTR-Gasket: Benchtop replaceable with a gasket seal



Filter Depth

- 2" Media Pack Thickness (2.88" frame height)
- 2.5" Media Pack Thickness (3.33" frame height)



Filter Depth

- 2.5" Media Pack Thickness (3.0" frame height)

STEP 3. Confirm filter efficiency:

- HEPA - IEST Type J 99.99% (most common)
- ULPA - IEST Type K 99.9995%

STEP 4. Measure filter media pack thickness:

- 2 in. (most common)
- 2.5 in.

STEP 5. Record your filter information using the table below:

Actual Width of Filter (inches)	Actual Length of Filter (inches)	Filter Seal Type	Filter Efficiency	Pack Thickness	Filter Part Number

Actual Width of Filter	Actual Length of Filter	Filter Seal Type	Filter Efficiency		Pack Thickness	Filter Part Number
19.81 in.	19.81 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042294-008
19.81 in.	31.81 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042294-020
19.81 in.	43.81 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042294-002
19.81 in.	19.81 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042294-008
19.81 in.	43.81 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042294-002
19.88 in.	19.88 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042299-029
19.88 in.	32.01 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042299-030
19.88 in.	38.07 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042299-031
19.88 in.	44.13 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042299-032
20.69 in.	20.69 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042299-020*
20.69 in.	32.69 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042299-021
20.69 in.	44.69 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042299-022*
21.31 in.	21.31 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042299-033
21.31 in.	33.44 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042299-034
21.31 in.	45.56 in.	RSR - Gel Seal	HEPA-2	IEST Type J - 99.99%	2"	042299-035
20.69 in.	20.69 in.	RSR - Gel Seal	HEPA- 2.5	IEST Type J - 99.99%	2.5"	042299-005*
20.69 in.	32.69 in.	RSR - Gel Seal	HEPA- 2.5	IEST Type J - 99.99%	2.5"	042299-006
20.69 in.	44.69 in.	RSR - Gel Seal	HEPA- 2.5	IEST Type J - 99.99%	2.5"	042299-007*
23.63 in.	23.63 in.	BTR - Gasket	HEPA- 2.5	IEST Type J - 99.99%	2.5"	042299-011
23.63 in.	35.63 in.	BTR - Gasket	HEPA- 2.5	IEST Type J - 99.99%	2.5"	042299-012
23.63 in.	47.63 in.	BTR - Gasket	HEPA- 2.5	IEST Type J - 99.99%	2.5"	042299-013*
19.81 in.	19.81 in.	RSR - Gel Seal	ULPA-2	IEST Type K - 99.9995%	2"	042294-009
19.81 in.	31.81 in.	RSR - Gel Seal	ULPA-2	IEST Type K - 99.9995%	2"	042294-021
19.81 in.	43.81 in.	RSR - Gel Seal	ULPA-2	IEST Type K - 99.9995%	2"	042294-003
19.81 in.	19.81 in.	RSR - Gel Seal	ULPA-2	IEST Type K - 99.9995%	2"	042294-009
19.81 in.	43.81 in.	RSR - Gel Seal	ULPA-2	IEST Type K - 99.9995%	2"	042294-003
20.69 in.	20.69 in.	RSR - Gel Seal	ULPA-2	IEST Type K - 99.9995%	2"	042299-017
20.69 in.	32.69 in.	RSR - Gel Seal	ULPA-2	IEST Type K - 99.9995%	2"	042299-018
20.69 in.	44.69 in.	RSR - Gel Seal	ULPA-2	IEST Type K - 99.9995%	2"	042299-019
20.69 in.	20.69 in.	RSR - Gel Seal	ULPA-2.5	IEST Type K - 99.9995%	2.5"	042299-008
20.69 in.	32.69 in.	RSR - Gel Seal	ULPA-2.5	IEST Type K - 99.9995%	2.5"	042299-009
20.69 in.	44.69 in.	RSR - Gel Seal	ULPA-2.5	IEST Type K - 99.9995%	2.5"	042299-010
23.63 in.	23.63 in.	BTR - Gasket	ULPA-2.5	IEST Type J - 99.99%	2.5"	042299-014
23.63 in.	35.63 in.	BTR - Gasket	ULPA-2.5	IEST Type J - 99.99%	2.5"	042299-015
23.63 in.	47.63 in.	BTR - Gasket	ULPA-2.5	IEST Type J - 99.99%	2.5"	042299-016

*Bolded line items are the most common sizes